

49-851R/1H Radius Glass Grip - Satin Stainless Steel 316 for Medium Grips Glass Thickness 1/4" or 3/8". Mounts to 1-1/2" Round Tube



Radius Glass Grips

ITEM #	MATERIAL	FINISH	N	H	GLASS THICKNESS	ROUND TUBE
SMALL GRIPS						
49-851R/1H	316	Satin	1.7"	1.87"	1/4" or 3/8"	1.875" Dia
MEDIUM GRIPS						
49-851R/2	316	Satin	1.7"	1.7"	3/8" or 1/2"	2.0" Dia
49-851R/1H	316	Satin	1.7"	1.7"	3/8" or 1/2"	1.75" Dia
49-851R/1	316	Satin	1.7"	1.7"	3/8" or 1/2"	1.5" Dia
LARGE GRIPS						
49-851R/3	316	Satin	2.38"	2.38"	3/8" or 1/2"	2.4" Dia
49-851R/2	316	Satin	2.38"	2.38"	3/8" or 1/2"	2" Dia
EXTRA LARGE GRIPS						
49-851R/4	316	Satin		3"	1/2" Dia	



Medium Grip Large Grip

Rubber Inserts for Radius Glass Grips

ITEM #	USE WITH	GLASS THICKNESS
49-22107	Small Grip	1/4"
49-22108	Small Grip	3/8"
49-22109	Medium Grip	1/4"
49-22110	Medium Grip	3/8"
49-22111	Large Grip	3/8"
49-22112	Large Grip	1/2"



- Rubber Inserts for Radius Glass Grips (Set of 2) Are Sold Separately. Item# GGI10.
- Glass clamps have a pin. The pin diameter is 6mm.

INSTALLATION Remove the side plate that is mounted with two screws and remove pin. Mount glass grip to tube using a M8 x 1.25 pitch screw, 20mm long. Replace pin, mount glass and then replace the side plate.