

49-851R/1H Radius Glass Grip - Satin Stainless Steel 316 for Medium Grips Glass Thickness 1/4" or 3/8". Mounts to 1-1/2" Round Tube



Radius Glass Grips

ITEM #	MATERIAL	FINISH	N	H	W	GLASS THICKNESS	ROUND TUBE
SMALL GRIPS							
49-851R/1H	316	Satin	1.7"	1.7"	1"	1/4" or 3/8"	1.875" Dia
MEDIUM GRIPS							
49-851R/2	316	Satin	1.7"	1.7"	3/4"	1/4" or 3/8"	2.625" Dia
49-851R/1H	316	Satin	1.7"	1.7"	3/4"	1/4" or 3/8"	1.875" Dia
49-851R/1H	316	Satin	1.7"	1.7"	3/4"	1/4" or 3/8"	1.875" Dia
LARGE GRIPS							
49-851R/3	316	Satin	2.38"	2.38"	1.5"	1/4" or 3/8"	3.625" Dia
49-851R/2	316	Satin	2.38"	2.38"	1.5"	1/4" or 3/8"	2" Dia
EXTRA LARGE GRIPS							
49-851R/4	316	Satin			3"	1/2" Tube	

Mounting Screws
Glass Clamps

Rubber Inserts for Radius Glass Grips

ITEM #	USE WITH	GLASS THICKNESS
GGI-007	Small Grips	1/4"
GGI-008	Small Grips	3/8"
GGI-009	Medium Grips	1/4"
GGI-010	Medium Grips	3/8"
GGI-011	Large Grips	3/8"
GGI-012	Large Grips	1/2"

- Rubber Inserts for Radius Glass Grips (Set of 2) Are Sold Separately. Item# GGI10.
- Glass clamps have a pin. The pin diameter is 6mm.

INSTALLATION Remove the side plate that is mounted with two screws and remove pin. Mount glass grip to tube using a M8 x 1.25 pitch screw, 20mm long. Replace pin, mount glass and then replace the side plate.