



49-850R/424 Radius Glass Grip - Satin Stainless Steel 316 for Small Grips Glass Thickness 1/4" or 3/8". Mounts to 1.67" Tube



Radius Glass Grips

ITEM #	MATERIAL	FINISH	W	H	D	GLASS THICKNESS	MOUNTS ON TO
SMALL GRIPS							
49-850R/424	316	Satin	1.5"	1.95"	1"	1/4" or 3/8"	1.67" Tube
MEDIUM GRIPS							
49-8516E	316	Satin	1.7"	1.7"	.94"	1/4" or 3/8"	Flat Surface
49-8519/1H	316	Satin	1.7"	1.7"	.94"	1/4" or 3/8"	1.5" Tube
49-8519/424	316	Satin	1.7"	1.7"	.94"	1/4" or 3/8"	1.67" Tube
LARGE GRIPS							
49-8609F	316	Satin	2.32"	6.36"	1.3"	1/4" or 3/8"	Flat Surface
49-8609J	316	Satin	2.32"	2.36"	1.3"	1/4" or 3/8"	2" Tube
EXTRA LARGE GRIPS							
49-8529/424	316	Satin				1/2"	1.67" Tube



Rubber Inserts for Radius Glass Grips

ITEM #	USE WITH	GLASS THICKNESS
85-G21007	Small Grips	1/4"
85-G21008	Small Grips	3/8"
85-G21009	Medium Grips	1/4"
85-G21010	Medium Grips	3/8"
85-G21013	Large Grips	3/8"
85-G21011	Large Grips	1/2"
85-G22015	Extra Large Grips	1/2"



- Rubber Inserts for Radius Glass Grips (Set of 2) Are Sold separately. Item# GGI10.
- Glass clamps have a pin. The pin diameter is 6mm.

INSTALLATION Remove the side plate that is mounted with two screws and remove pin. Mount glass grip to tube using a M8 x 1.25 pitch screw, 20mm long. Replace pin, mount glass and then replace the side plate.